



Pushing Performance  
Since 1945

# Han-INOX 3A-SMH-M20



Image is for illustration purposes only. Please refer to product description.

|                    |                                                                               |
|--------------------|-------------------------------------------------------------------------------|
| Part number        | 19 44 003 1250                                                                |
| Specification      | Han-INOX 3A-SMH-M20                                                           |
| HARTING eCatalogue | <a href="https://harting.com/19440031250">https://harting.com/19440031250</a> |

## Identification

|                             |                         |
|-----------------------------|-------------------------|
| Category                    | Hoods / Housings        |
| Series of hoods/housings    | Han-INOX®               |
| Type of hood/housing        | Surface mounted housing |
| Description of hood/housing | With seal               |

## Version

|                         |                                       |
|-------------------------|---------------------------------------|
| Size                    | 3 A                                   |
| Version                 | Side entry                            |
| Number of cable entries | 1                                     |
| Cable entry             | 1x M20                                |
| Locking type            | Single locking lever                  |
| Field of application    | Hoods/housings for harsh environments |
| Pack contents           | With seal screw                       |

## Technical characteristics

|                                        |                                                |
|----------------------------------------|------------------------------------------------|
| Limiting temperature                   | -40 ... +125 °C                                |
| Note on the limiting temperature       | For use as a connector according to IEC 61984. |
| Degree of protection acc. to IEC 60529 | IP44                                           |
|                                        | IP65 With seal screw                           |
|                                        | IP66 With seal screw                           |
|                                        | IP67 With seal screw                           |
| Type rating acc. to UL 50 / UL 50E     | 4                                              |
|                                        | 4X                                             |
|                                        | 12                                             |



**Pushing Performance**  
Since 1945

## Material properties

|                                      |                       |
|--------------------------------------|-----------------------|
| Material (hood/housing)              | Stainless steel       |
| Surface (hood/housing)               | Uncoated              |
| Colour (hood/housing)                | Unpainted             |
| Material (seal)                      | NBR                   |
| Material (locking)                   | Stainless steel       |
| RoHS                                 | compliant             |
| ELV status                           | compliant             |
| China RoHS                           | e                     |
| REACH Annex XVII substances          | Not contained         |
| REACH ANNEX XIV substances           | Not contained         |
| REACH SVHC substances                | Not contained         |
| California Proposition 65 substances | Yes                   |
| California Proposition 65 substances | Nickel<br>Naphthalene |

## Specifications and approvals

|           |                                                            |
|-----------|------------------------------------------------------------|
| UL / CSA  | UL 1977 ECBT2.E235076<br>CSA-C22.2 No. 182.3 ECBT8.E235076 |
| Approvals | CE<br>DNV GL                                               |

## Commercial data

|                                |                                          |
|--------------------------------|------------------------------------------|
| Packaging size                 | 1                                        |
| Net weight                     | 23.25 g                                  |
| Country of origin              | Germany                                  |
| European customs tariff number | 85389099                                 |
| GTIN                           | 5713140131965                            |
| eCl@ss                         | 27440202 Shell for industrial connectors |
| ETIM                           | EC000437                                 |
| UNSPSC 24.0                    | 39121466                                 |