

UICIT_PL 8_M32



Image is for illustration purposes only. Please refer to product description.

Part number	19 58 001 1450
Specification	UICIT_PL 8_M32
HARTING eCatalogue	https://harting.com/19580011450

Identification

Category	Hoods / Housings
Series	HARTING UIC
Identification	UIC IT
Type of hood/housing	Hood

Version

Number of contacts	8
Version	Top entry
Number of cable entries	1
Cable entry	1x M32
Field of application	Hoods/housings for harsh outdoor environments

Technical characteristics

Limiting temperature	-50 ... +125 °C
Degree of protection acc. to IEC 60529	IP67 / IP69

Material properties

Material (hood/housing)	Polyamide (PA) Fibre-glass reinforced
Colour (hood/housing)	RAL 6005 (moos green)
Material (seal)	Silicone
Material flammability class acc. to UL 94	V-0
RoHS	compliant

Material properties

ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Specifications and approvals

Specifications	UIC 50558 IRS 50558 IEC 61373 Category 2 IEC 60529
----------------	---

Commercial data

Packaging size	1
Net weight	140 g
Country of origin	India
European customs tariff number	85389099
eCl@ss	27440202 Shell for industrial connectors
ETIM	EC000437
UNSPSC 24.0	39121466