

ICC20_1_I_SMC_F_FP_CRT




Image is for illustration purposes only. Please refer to product description.

Part number	19 59 020 0102
Specification	ICC20_1_I_SMC_F_FP_CRT
HARTING eCatalogue	https://harting.com/19590200102

Identification

Category	Connectors
Series	HARTING ICC
Element	Inserts

Version

Termination method	Crimp termination
Gender	Female
Size	20
Number of contacts	1
Details	Please order crimp contacts separately.

Technical characteristics

Conductor cross-section (mm²)	95 ... 150 mm²
Rated current	400 A
Rated voltage	600 V
Pollution degree	3
Insulation resistance	$>10^{10} \Omega$
Limiting temperature	-40 ... +125 °C
Mating cycles	≥500

Material properties

Material (insert)	Polycarbonate (PC)
Colour (insert)	RAL 7032 (pebble grey)



Pushing Performance
Since 1945

Material properties

Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Specifications and approvals

Specifications	IEC 61984 IEC 60664-1
Approvals	CE

Commercial data

Packaging size	1
Net weight	16.5 g
Country of origin	India
European customs tariff number	85366990
GTIN	5713140491069
eCl@ss	27440223 Contact insert for circular connectors
UNSPSC 24.0	39121421