

ICC20 Jam-Nut Receptacle



Image is for illustration purposes only. Please refer to product description.

Identification

Category	Connectors
Series	HARTING ICC
Type of hood/housing	Bulkhead mounted housing
Description of hood/housing	Straight Rear mounting incl. lock nut

Version

Size	20
Locking type	Bayonet locking
Details	Please order backshell or fixing nut separately.

Technical characteristics

Tightening torque	15 Nm Lock nut
Limiting temperature	-40 ... +125 °C
Number of relockings	≥500
Degree of protection acc. to IEC 60529	IP67 IPX9

Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Nickel plated
Material (seal)	EPDM
Colour (seal)	Black

Material properties

RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Specifications and approvals

Specifications	IEC 61984 IEC 60664-1
Approvals	CE

Commercial data

Packaging size	1
Net weight	85.6 g
Country of origin	India
European customs tariff number	85389099
GTIN	5713140400566
eCl@ss	27440224 Shell for circular connectors
UNSPSC 24.0	39121405