

## ICC20 Backshell straight (17-20,5 mm)



Image is for illustration purposes only. Please refer to product description.

Part number	19 59 120 4013
Specification	ICC20 Backshell straight (17-20,5 mm)
HARTING eCatalogue	<a href="https://harting.com/19591204013">https://harting.com/19591204013</a>

### Identification

Category	Connectors
Series	HARTING ICC
Type of hood/housing	Backshell
Description of hood/housing	With integrated cable gland Straight

### Version

Size	20
Version	Top entry

### Technical characteristics

Tightening torque	12 Nm Cable gland 15 Nm Backshell
Limiting temperature	-40 ... +125 °C
Number of relockings	≥10
Degree of protection acc. to IEC 60529	IP67 IPX9
Clamping range	17 ... 20.5 mm

### Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Nickel plated
Material (seal)	TPE
Colour (seal)	Brown

## Material properties

RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

## Specifications and approvals

Specifications	IEC 61984 IEC 60664-1
Approvals	CE

## Commercial data

Packaging size	1
Net weight	0.095 kg
Country of origin	India
European customs tariff number	85389099
GTIN	5713140400597
eCl@ss	27440224 Shell for circular connectors
UNSPSC 24.0	39121405