

Acces. Special Cable Clamp EMC M40



Image is for illustration purposes only. Please refer to product description.

Part number	19 62 000 5097
Specification	Acces. Special Cable Clamp EMC M40
HARTING eCatalogue	https://harting.com/19620005097

Identification

Category	Accessories
Type of accessory	Cable gland
Description of the accessory	EMC version

Technical characteristics

Wrench size	43
Limiting temperature	-40 ... +130 °C
Degree of protection acc. to IEC 60529	IP68
Size	M40
Clamping range	17 ... 20.5 mm
Shielding diameter	15 ... 20 mm
Width across corners	47.3 mm

Material properties

Material (cable glands)	Metal
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes



Pushing Performance
Since 1945

Material properties

REACH SVHC substances	Lead
	2-(2'-Hydroxy-3'-tert-butyl-5'-methylphenyl)-5-chlorobenzotriazole (UV-326)
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead
	Nickel

Commercial data

Packaging size	1
Net weight	149.7 g
Country of origin	Germany
European customs tariff number	74122000
GTIN	5713140132252
eCl@ss	27140803 Cable gland EMC (electrical installation)
ETIM	EC000441
UNSPSC 24.0	39121431