

## Han CGM-M-Rail EMC M50 32-42 mm



Image is for illustration purposes only. Please refer to product description.

### Identification

Category	Accessories
Series of hoods/housings	Han® CGM-M-Rail
Type of accessory	Cable gland
Description of the accessory	EMC version Railway version

### Technical characteristics

Tightening torque	30 Nm
Wrench size	57
Limiting temperature	-40 ... +100 °C
Degree of protection acc. to IEC 60529	IP66 IP68 IP69
Size	M50
Clamping range	32 ... 42 mm
Width across corners	61 mm

### Material properties

Material (cable glands)	Brass
Material (seal)	EPDM
Surface (accessories)	Nickel plated
RoHS	compliant
ELV status	compliant
China RoHS	e

## Material properties

REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

## Specifications and approvals

Approvals	DNV GL
-----------	--------

## Commercial data

Packaging size	1
Net weight	317 g
Country of origin	Germany
European customs tariff number	74122000
GTIN	5713140537828
eCl@ss	27140801 Screwed cable gland (electrical)
UNSPSC 24.0	39121431