

Han CGM-M-Rail EMC M32 16-25 mm



Image is for illustration purposes only. Please refer to product description.

Part number	19 62 000 7124
Specification	Han CGM-M-Rail EMC M32 16-25 mm
HARTING eCatalogue	https://harting.com/19620007124

Identification

Category	Accessories
Series of hoods/housings	Han® CGM-M-Rail
Type of accessory	Cable gland
Description of the accessory	EMC version Railway version

Technical characteristics

Tightening torque	15 Nm
Wrench size	36
Limiting temperature	-40 ... +100 °C
Degree of protection acc. to IEC 60529	IP66 IP68 IP69
Size	M32
Clamping range	16 ... 25 mm
Width across corners	39.5 mm

Material properties

Material (cable glands)	Brass
Material (seal)	EPDM
Surface (accessories)	Nickel plated
RoHS	compliant
ELV status	compliant
China RoHS	e

Material properties

REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

Specifications and approvals

Approvals	DNV GL
-----------	--------

Commercial data

Packaging size	1
Net weight	111.8 g
Country of origin	Germany
European customs tariff number	74122000
GTIN	5713140532090
eCl@ss	27140801 Screwed cable gland (electrical)
UNSPSC 24.0	39121431