

## Han 3 EMC Hood M25



Image is for illustration purposes only. Please refer to product description.

|                    |                                                                               |
|--------------------|-------------------------------------------------------------------------------|
| Part number        | 19 62 003 1445                                                                |
| Specification      | Han 3 EMC Hood M25                                                            |
| HARTING eCatalogue | <a href="https://harting.com/19620031445">https://harting.com/19620031445</a> |

### Identification

|                          |                  |
|--------------------------|------------------|
| Category                 | Hoods / Housings |
| Series of hoods/housings | Han® EMC         |
| Type of hood/housing     | Hood             |

### Version

|                         |                                            |
|-------------------------|--------------------------------------------|
| Size                    | 3 A                                        |
| Version                 | Top entry                                  |
| Number of cable entries | 1                                          |
| Cable entry             | 1x M25                                     |
| Locking type            | Single locking lever                       |
| Field of application    | Hoods/Housings for higher EMC requirements |
| Pack contents           | Please order seal screw separately.        |

### Technical characteristics

|                                        |                                                      |
|----------------------------------------|------------------------------------------------------|
| Limiting temperature                   | -40 ... +125 °C                                      |
| Note on the limiting temperature       | For use as a connector according to IEC 61984.       |
| Degree of protection acc. to IEC 60529 | IP44<br>IP65 With seal screw<br>IP67 With seal screw |
| Type rating acc. to UL 50 / UL 50E     | 12                                                   |

### Material properties

|                         |               |
|-------------------------|---------------|
| Material (hood/housing) | Zinc die-cast |
| Surface (hood/housing)  | Uncoated      |



**Pushing Performance**  
Since 1945

## Material properties

|                                      |                |
|--------------------------------------|----------------|
| Colour (hood/housing)                | Unpainted      |
| RoHS                                 | compliant      |
| ELV status                           | compliant      |
| China RoHS                           | e              |
| REACH Annex XVII substances          | Not contained  |
| REACH ANNEX XIV substances           | Not contained  |
| REACH SVHC substances                | Not contained  |
| California Proposition 65 substances | Yes            |
| California Proposition 65 substances | Lead<br>Nickel |

## Specifications and approvals

|           |              |
|-----------|--------------|
| Approvals | CE<br>DNV GL |
|-----------|--------------|

## Commercial data

|                                |                                          |
|--------------------------------|------------------------------------------|
| Packaging size                 | 1                                        |
| Net weight                     | 78.333 g                                 |
| Country of origin              | China                                    |
| European customs tariff number | 85389099                                 |
| GTIN                           | 5713140132351                            |
| eCl@ss                         | 27440202 Shell for industrial connectors |
| ETIM                           | EC000437                                 |
| UNSPSC 24.0                    | 39121466                                 |