

Han 24EMC/B-HTE-3xM25 (HT)



Image is for illustration purposes only. Please refer to product description.

Identification

| | |
|--------------------------|--|
| Category | Hoods / Housings |
| Series of hoods/housings | <u>Han® EMC/B</u> <u>Han® High Temp</u> |
| Type of hood/housing | Hood |
| Type | High construction |

Version

| | |
|-------------------------|--|
| Size | 24 B |
| Version | Top entry |
| Number of cable entries | 3 |
| Cable entry | 3x M25 |
| Locking type | Double locking lever |
| Field of application | Hoods/Housings for higher EMC requirements |

Technical characteristics

| | |
|--|---|
| Limiting temperature | -40 ... +125 °C -40 ... +200 °C With Han® High Temp components |
| Note on the limiting temperature | For use as a connector according to IEC 61984. |
| Mating cycles | ≥500 |
| Degree of protection acc. to IEC 60529 | IP65 IP66 |
| Type rating acc. to UL 50 / UL 50E | 4 12 |

Material properties

| | |
|--------------------------------------|--------------------|
| Material (hood/housing) | Aluminium die-cast |
| Surface (hood/housing) | Uncoated |
| Colour (hood/housing) | Unpainted |
| RoHS | compliant |
| ELV status | compliant |
| China RoHS | e |
| REACH Annex XVII substances | Not contained |
| REACH ANNEX XIV substances | Not contained |
| REACH SVHC substances | Not contained |
| California Proposition 65 substances | Yes |

Specifications and approvals

| | |
|-----------|--|
| UL / CSA | UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076 |
| Approvals | CE DNV GL |

Commercial data

| | |
|--------------------------------|--|
| Packaging size | 1 |
| Net weight | 245 g |
| Country of origin | Germany |
| European customs tariff number | 85389099 |
| GTIN | 5713140172067 |
| eCl@ss | 27440202 Shell for industrial connectors |
| ETIM | EC000437 |
| UNSPSC 24.0 | 39121466 |