

preLink Terminal mod AWG26/27 white 1=10



Image is for illustration purposes only. Please refer to product description.

Part number	20 82 000 0003
Specification	preLink Terminal mod AWG26/27 white 1=10
HARTING eCatalogue	https://harting.com/2082000003

Identification

Category	Connectors
Series	preLink®
Element	Termination block
Specification	8 poles

Version

Termination method	preLink® IDC insulation displacement termination
Pack contents	10 pieces

Technical characteristics

Conductor cross-section	0.1 ... 0.12 mm ²
Conductor cross-section [AWG]	AWG 27 ... AWG 26
Wire outer diameter	0.8 ... 1.1 mm
Limiting temperature	-40 ... +85 °C
Mating cycles	≥10
Vibration resistance	5.72 m/s ² acc. to IEC 61373 Category 1 Class B
Shock resistance	5 g / 30 ms, 5 shocks / axis and direction acc. to IEC 61373 Category 1 Class B

Material properties

Colour (insert)	White
RoHS	compliant
ELV status	compliant
China RoHS	e



Pushing Performance
Since 1945

Material properties

REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained

Specifications and approvals

Specifications	EN 45545-2
UL / CSA	UL 1863 DUXR2.E470046 CSA-C22.2 No. 182.4, No. 233-09 DUXR8.E470046
Approvals	DNV GL
PROFINET	Yes

Commercial data

Packaging size	1
Net weight	13 g
Country of origin	Latvia
European customs tariff number	85366990
GTIN	5713140135482
eCl@ss	27440291 Connector component (parts)
ETIM	EC002943
UNSPSC 24.0	39121400