



Pushing Performance
Since 1945

preLink Terminal mod AWG22/24 black 1=10



Image is for illustration purposes only. Please refer to product description.

Part number	20 82 000 0005
Specification	preLink Terminal mod AWG22/24 black 1=10
HARTING eCatalogue	https://harting.com/20820000005

Identification

Category	Connectors
Series	preLink®
Element	Termination block
Specification	4 poles AIDA compliant

Version

Termination method	preLink® IDC insulation displacement termination
Pack contents	10 pieces

Technical characteristics

Conductor cross-section (mm²)	0.22 ... 0.32 mm²
Conductor cross-section (AWG)	AWG 24 ... AWG 22
Wire outer diameter	1.3 ... 1.6 mm
Limiting temperature	-40 ... +85 °C
Mating cycles	≥10
Vibration resistance	5.72 m/s² acc. to IEC 61373 Category 1 Class B
Shock resistance	5 g / 30 ms, 5 shocks / axis and direction acc. to IEC 61373 Category 1 Class B

Material properties

Colour (insert)	Black
RoHS	compliant
ELV status	compliant



Pushing Performance
Since 1945

Material properties

China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained

Specifications and approvals

Specifications	EN 45545-2
Approvals	DNV GL
PROFINET	Yes

Commercial data

Packaging size	1
Net weight	17 g
Country of origin	Latvia
European customs tariff number	85366990
GTIN	5713140224230
eCl@ss	27440291 Connector component (parts)
ETIM	EC002943
UNSPSC 24.0	39121400

Wire map

