

## M12-ACC-CRIMP FLANGESET6x7/14x7.4x2/9x10



Image is for illustration purposes only. Please refer to product description.

Part number	21 01 010 0026
Specification	M12-ACC-CRIMP FLANGESET6x7/14x7.4x2/9x10
HARTING eCatalogue	<a href="https://harting.com/21010100026">https://harting.com/21010100026</a>

### Identification

Category	Accessories
Series	Circular connectors M12
Identification	Slim Design
Type of accessory	Crimp flange set

### Version

Details	HARTING offers to test and define the best crimp flange and ferrule combination for customer specific cables.
---------	---

### Technical characteristics

Ambient temperature	-40 ... +85 °C
---------------------	----------------

### Material properties

RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

## Material properties

Fire protection on railway vehicles	EN 45545-2 (2020-08) + A1 (2023-10)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

## Commercial data

Packaging size	1
Net weight	6.5 g
Country of origin	Romania
European customs tariff number	85366990
GTIN	5713140236172
eCl@ss	27440292 Connector component (accessories)
ETIM	EC002943
UNSPSC 24.0	39121400