

M12-P-ACC-HOUSING REAR MOUNTING (30 pcs)



Image is for illustration purposes only. Please refer to product description.

Part number	21 03 302 1000 407
Specification	M12-P-ACC-HOUSING REAR MOUNTING (30 pcs)
HARTING eCatalogue	https://harting.com/21033021000407

Identification

Category	Accessories
Series	Circular connectors M12
Type of accessory	Housing
Description of the accessory	for rear mounting

Version

Gender	Male
Locking type	Screw locking PushPull

Technical characteristics

Tightening torque	2 Nm Lock nut
Degree of protection acc. to IEC 60529	IP65 / IP67 mated condition

Material properties

RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead



Pushing Performance
Since 1945

Material properties

ECHA SCIP number	0d7d3693-d625-47ab-934a-d241bf72c86e
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead
Fire protection on railway vehicles	EN 45545-2 (2020-08) + A1 (2023-10)
Requirement set with Hazard Levels	R26

Specifications and approvals

Specifications	IEC 61076-2-010
UL / CSA	UL 1977 ECBT2.E102079 CSA-C22.2 No. 182.3 ECBT8.E102079
PROFINET	Yes

Commercial data

Packaging size	30
Net weight	10 g
Country of origin	Romania
European customs tariff number	85389099
GTIN	5713140236363
eCl@ss	27440292 Connector component (accessories)
ETIM	EC002943
UNSPSC 24.0	39121400