

PFT M12-crimp shielded male B-Code 5pol



Image is for illustration purposes only. Please refer to product description.

Part number	21 03 841 1525
Specification	PFT M12-crimp shielded male B-Code 5pol
HARTING eCatalogue	https://harting.com/21038411525

Identification

Category	Connectors
Series	Circular connectors M12
Element	Cable connector Panel feed through
Specification	for rear mounting

Version

Termination method	Crimp termination
Gender	Male
Shielding	Shielded
Number of contacts	5
Coding	B-coding
Locking type	Screw locking
Details	Please order crimp contacts separately.

Technical characteristics

Conductor cross-section	0.14 ... 0.75 mm ²
Conductor cross-section [AWG]	AWG 26 ... AWG 18
Wire outer diameter	≤2.3 mm
Rated current	4 A
Rated voltage	60 V
Rated impulse voltage	1.5 kV
Pollution degree	3



Pushing Performance
Since 1945

Technical characteristics

Overvoltage category	III
Insulation resistance	$>10^8 \Omega$
Contact resistance	$\leq 10 \text{ m}\Omega$
Tightening torque	2 Nm Lock nut
Limiting temperature	-40 ... +85 °C
Mating cycles	≥ 500
Degree of protection acc. to IEC 60529	IP65 / IP67 mated condition
Cable diameter	4.5 ... 8.8 mm
Isolation group	I ($600 \leq \text{CTI}$)
Thickness of the panel	2.5 ... 4.5 mm

Material properties

Material (insert)	Polyamide (PA)
Material (hood/housing)	Zinc die-cast
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	0d7d3693-d625-47ab-934a-d241bf72c86e
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel
Fire protection on railway vehicles	EN 45545-2 (2020-08) + A1 (2023-10)
Requirement set with Hazard Levels	R26

Specifications and approvals

Specifications	IEC 61076-2-101
UL / CSA	UL 1977 ECBT2.E102079 CSA-C22.2 No. 182.3 ECBT8.E102079



Pushing Performance
Since 1945

Commercial data

Packaging size	1
Net weight	45 g
Country of origin	Romania
European customs tariff number	85366990
GTIN	5713140139671
eCl@ss	27440116 Circular connector (for field assembly)
ETIM	EC002635
UNSPSC 24.0	39121413