

M17 Crimp Contact 1,0mm, FE ,0,75-1,0mm²



Image is for illustration purposes only. Please refer to product description.

Part number	21 17 070 0000
Specification	M17 Crimp Contact 1,0mm, FE ,0,75-1,0mm²
HARTING eCatalogue	https://harting.com/21170700000

Identification

Category	Contacts
Series	Circular connectors M17
Type of contact	Crimp contact

Version

Termination method	Crimp termination
Gender	Female
Manufacturing process	Turned contacts

Technical characteristics

Conductor cross-section	0.75 ... 1 mm²
Conductor cross-section [AWG]	AWG 19 ... AWG 17
Stripping length	5 mm
Limiting temperature	-40 ... +125 °C

Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Gold plated
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained

Packaging size	100
Net weight	0.183 g
Country of origin	Romania
European customs tariff number	85366990
GTIN	5713140819740
eCl@ss	27440204 Contact for industrial connectors
ETIM	EC000796
UNSPSC 24.0	39121522