

## M17 Crimp Contact 1,0mm,male,1,5mm<sup>2</sup>



Part number	21 17 071 0000
Specification	M17 Crimp Contact 1,0mm,male,1,5mm <sup>2</sup>
HARTING eCatalogue	<a href="https://harting.com/21170710000">https://harting.com/21170710000</a>

Image is for illustration purposes only. Please refer to product description.

### Identification

Category	Contacts
Series	Circular connectors M17
Type of contact	Crimp contact

### Version

Termination method	Crimp termination
Gender	Male
Manufacturing process	Turned contacts

### Technical characteristics

Conductor cross-section	1 ... 1.5 mm <sup>2</sup>
Conductor cross-section [AWG]	AWG 18 ... AWG 16
Stripping length	5 mm
Limiting temperature	-40 ... +125 °C

### Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Gold plated
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained

## Material properties

REACH SVHC substances	Not contained
-----------------------	---------------

## Commercial data

Packaging size	100
Net weight	0.3 g
Country of origin	Romania
European customs tariff number	85366990
GTIN	5713140819733
eCl@ss	27440204 Contact for industrial connectors
ETIM	EC000796
UNSPSC 24.0	39121522