

M17-CCH-SCR-STR-SHLD-10-13mm



Image is for illustration purposes only. Please refer to product description.

Part number	21 17 100 0300
Specification	M17-CCH-SCR-STR-SHLD-10-13mm
HARTING eCatalogue	https://harting.com/21171000300

Identification

Category	Connectors
Series	Circular connectors M17
Type of hood/housing	Cable housing

Version

Size	M17
Shielding	Shielded
Version	Top entry
Locking type	Screw locking

Technical characteristics

Limiting temperature	-40 ... +125 °C
Number of relockings	≥500
Degree of protection acc. to IEC 60529	IP66 / IP67 screwed / locked condition
Clamping range	10 ... 13 mm

Material properties

Material (hood/housing)	Copper-zinc alloy
Surface (hood/housing)	Nickel plated
Material (seal)	NBR
Colour (seal)	Black
RoHS	compliant
ELV status	compliant



Pushing Performance
Since 1945

Material properties

China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Specifications and approvals

Specifications	IEC 61984 IEC 60664-1
UL / CSA	UL 2237 / 2238 in preparation
Approvals	CE

Commercial data

Packaging size	1
Net weight	60 g
Country of origin	Romania
European customs tariff number	73181595
GTIN	5713140819634
eCl@ss	27440224 Shell for circular connectors
UNSPSC 24.0	39121405