

## M17-COUPH-SCR/BAY-STR-SHLD-6.5-10mm



Image is for illustration purposes only. Please refer to product description.

### Identification

Category	Connectors
Series	Circular connectors M17
Type of hood/housing	Cable to cable housing

### Version

Size	M17
Shielding	Shielded
Version	Top entry
Locking type	Screw locking Toggle locking

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Number of relockings	≥500
Degree of protection acc. to IEC 60529	IP66 / IP67 screwed / locked condition
Clamping range	6.5 ... 10 mm

### Material properties

Material (hood/housing)	Copper-zinc alloy
Surface (hood/housing)	Nickel plated
Material (seal)	NBR
Colour (seal)	Black
RoHS	compliant

## Material properties

ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

## Specifications and approvals

Specifications	IEC 61984 IEC 60664-1
UL / CSA	UL 2237 / 2238 in preparation
Approvals	CE

## Commercial data

Packaging size	1
Net weight	40 g
Country of origin	Romania
European customs tariff number	73181595
GTIN	5713140819597
eCl@ss	27440224 Shell for circular connectors
UNSPSC 24.0	39121405