

## M17-DEVH-SCR/BAY-STR-FM-M18X0.75



Image is for illustration purposes only. Please refer to product description.

Part number	21 17 200 4600
Specification	M17-DEVH-SCR/BAY-STR-FM-M18X0.75
HARTING eCatalogue	<a href="https://harting.com/21172004600">https://harting.com/21172004600</a>

### Identification

Category	Connectors
Series	Circular connectors M17
Type of hood/housing	Flange housing
Description of hood/housing	Front mounting

### Version

Size	M17
Shielding	Shielded
Version	Top entry
Locking type	Screw locking Toggle locking

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Number of relockings	≥500
Degree of protection acc. to IEC 60529	IP66 / IP67 screwed / locked condition

### Material properties

Material (hood/housing)	Copper-zinc alloy
Surface (hood/housing)	Nickel plated
Material (seal)	Viton
Colour (seal)	Black
RoHS	compliant with exemption



Pushing Performance  
Since 1945

## Material properties

RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel Lead
Fire protection on railway vehicles	EN 45545-2 (2020-08) + A1 (2023-10)
Requirement set with Hazard Levels	no requirements (flammable mass < 10g)

## Specifications and approvals

Specifications	IEC 61984 IEC 60664-1
UL / CSA	UL 2237 / 2238 in preparation
Approvals	CE

## Commercial data

Packaging size	1
Net weight	23.764 g
Country of origin	Romania
European customs tariff number	85366990
GTIN	5713140422308
eCl@ss	27440224 Shell for circular connectors
UNSPSC 24.0	39121405