

M17-INS-SIG-CRT-17P-MA



Image is for illustration purposes only. Please refer to product description.

Part number	21 17 505 0000
Specification	M17-INS-SIG-CRT-17P-MA
HARTING eCatalogue	https://harting.com/21175050000

Identification

Category	Inserts
Series	Circular connectors M17
Identification	Signal
Element	Inserts

Version

Termination method	Crimp termination
Gender	Male
Number of contacts	17
Number of signal contacts	17

Technical characteristics

Rated current	3.6 A
Rated voltage	63 V
Rated impulse voltage	1.5 kV
Pollution degree	3
Limiting temperature	-40 ... +125 °C
Mating cycles	≥500

Material properties

Material (insert)	Polyamide (PA)
Colour (insert)	Black
Material flammability class acc. to UL 94	V-0



Pushing Performance
Since 1945

Material properties

RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained

Specifications and approvals

Specifications	IEC 61984
	IEC 60664-1
UL / CSA	UL 2237 / 2238 in preparation
Approvals	CE

Commercial data

Packaging size	1
Net weight	2.9 g
Country of origin	Romania
European customs tariff number	85366990
GTIN	5713140819511
eCl@ss	27440223 Contact insert for circular connectors
ETIM	EC003557
UNSPSC 24.0	39121421