

M17-INS-POW-CRT-4P-3+PE-FE



Image is for illustration purposes only. Please refer to product description.

Part number	21 17 522 0000
Specification	M17-INS-POW-CRT-4P-3+PE-FE
HARTING eCatalogue	https://harting.com/21175220000

Identification

Category	Inserts
Series	Circular connectors M17
Identification	Power
Element	Inserts

Version

Termination method	Crimp termination
Gender	Female
Number of contacts	4
Number of power contacts	3
Number of special contacts	1x PE contact

Technical characteristics

Rated current	20 A
Rated voltage	630 V
Rated impulse voltage	6 kV
Pollution degree	3
Rated voltage acc. to UL	600 V
Rated voltage acc. to CSA	600 V
Limiting temperature	-40 ... +125 °C
Mating cycles	≥500



Pushing Performance
Since 1945

Material properties

Material (insert)	Polyamide (PA)
Colour (insert)	Black
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained

Specifications and approvals

Specifications	IEC 61984
	IEC 60664-1
UL / CSA	UL 2237 / 2238 in preparation
Approvals	CE

Commercial data

Packaging size	1
Net weight	0.01 g
Country of origin	Romania
European customs tariff number	85366990
GTIN	5713140819481
eCl@ss	27440223 Contact insert for circular connectors
ETIM	EC003557
UNSPSC 24.0	39121421