

M12 X coded cable Assembly;10m



Image is for illustration purposes only. Please refer to product description.

| | |
|--------------------|---|
| Part number | 21 33 010 0850 100 |
| Specification | M12 X coded cable Assembly;10m |
| HARTING eCatalogue | https://harting.com/21330100850100 |

Identification

| | |
|---------------|-------------------------------|
| Category | System cabling |
| Series | Circular connectors M12 |
| Element | Cable assemblies |
| Specification | Pre-assembled on one side |
| Connector 1 | M12 X-coding Male Straight |
| Type of cable | Copper cable (round) |

Version

| | |
|-----------------|-------------------|
| Cable length | 10 m |
| Number of cores | 8 |
| Core structure | 4x 2 Twisted Pair |
| Shielding | Shielded |
| Coding | X-coding |

Technical characteristics

| | |
|------------------------------|--|
| Transmission characteristics | Cat. 6 _A Class E _A up to 500 MHz |
| Data rate | 10 Mbit/s 100 Mbit/s 1 Gbit/s 2.5 Gbit/s 5 Gbit/s 10 Gbit/s |
| Limiting temperature | -40 ... +70 °C |



Pushing Performance
Since 1945

Material properties

| | |
|--------------------------------------|--|
| Material (cable) | PUR (polyurethane) |
| Colour (cable) | Yellow |
| RoHS | compliant with exemption |
| RoHS exemptions | 6(c): Copper alloy containing up to 4 % lead by weight |
| ELV status | compliant with exemption |
| China RoHS | 50 |
| REACH Annex XVII substances | Not contained |
| REACH ANNEX XIV substances | Not contained |
| REACH SVHC substances | Yes |
| REACH SVHC substances | Lead |
| California Proposition 65 substances | Yes |
| California Proposition 65 substances | Lead Nickel |

Commercial data

| | |
|--------------------------------|--|
| Packaging size | 2 |
| Net weight | 534.25 g |
| Country of origin | Germany |
| European customs tariff number | 85444290 |
| GTIN | 5713140140233 |
| eCl@ss | 27060390 Ready-made data cable (unspecified) |
| ETIM | EC002599 |
| UNSPSC 24.0 | 26121600 |