

## M12 L-coded Cable Assembly 10m



Image is for illustration purposes only. Please refer to product description.

|                    |                                                                                     |
|--------------------|-------------------------------------------------------------------------------------|
| Part number        | 21 33 A70 0524 100                                                                  |
| Specification      | M12 L-coded Cable Assembly 10m                                                      |
| HARTING eCatalogue | <a href="https://harting.com/2133A700524100">https://harting.com/2133A700524100</a> |

### Identification

|               |                                 |
|---------------|---------------------------------|
| Category      | System cabling                  |
| Series        | Circular connectors M12         |
| Element       | Cable assemblies                |
| Specification | Pre-assembled on one side       |
| Connector 1   | M12 L-coding<br>Female Straight |
| Type of cable | Copper cable (round)            |

### Version

|                 |                        |
|-----------------|------------------------|
| Cable length    | 10 m                   |
| Number of cores | 5                      |
| Core structure  | 5x 2.5 mm <sup>2</sup> |
| Coding          | L-coding               |

### Technical characteristics

|                      |                |
|----------------------|----------------|
| Limiting temperature | -40 ... +80 °C |
|----------------------|----------------|

### Material properties

|                  |                                                        |
|------------------|--------------------------------------------------------|
| Material (cable) | PVC                                                    |
| Colour (cable)   | Grey                                                   |
| RoHS             | compliant with exemption                               |
| RoHS exemptions  | 6(c): Copper alloy containing up to 4 % lead by weight |
| ELV status       | compliant with exemption                               |



**Pushing Performance**  
Since 1945

## Material properties

|                                      |                |
|--------------------------------------|----------------|
| China RoHS                           | 50             |
| REACH Annex XVII substances          | Not contained  |
| REACH ANNEX XIV substances           | Not contained  |
| REACH SVHC substances                | Yes            |
| REACH SVHC substances                | Lead           |
| California Proposition 65 substances | Yes            |
| California Proposition 65 substances | Lead<br>Nickel |

## Commercial data

|                                |                                              |
|--------------------------------|----------------------------------------------|
| Packaging size                 | 1                                            |
| Net weight                     | 1 g                                          |
| Country of origin              | Romania                                      |
| European customs tariff number | 85444290                                     |
| GTIN                           | 5713140240278                                |
| eCl@ss                         | 27060390 Ready-made data cable (unspecified) |
| ETIM                           | EC002599                                     |
| UNSPSC 24.0                    | 26121600                                     |