

## Size 15 6-pol st/- m/- PUR 1,5mm<sup>2</sup> 1,0m



Part number	21 34 280 0641 010
Specification	Size 15 6-pol st/- m/- PUR 1,5mm <sup>2</sup> 1,0m
HARTING eCatalogue	<a href="https://harting.com/21342800641010">https://harting.com/21342800641010</a>

Image is for illustration purposes only. Please refer to product description.

### Identification

Category	System cabling
Series	Circular connectors Size 15
Element	Cable assemblies
Specification	Pre-assembled on one side
Connector 1	Size 15 Male Straight
Type of cable	Copper cable (round)

### Version

Cable length	1 m
Number of cores	6
Core structure	6x 1.5 mm <sup>2</sup>

### Technical characteristics

Rated current (signal)	10 A
Rated voltage (signal)	63 V AC/DC
Rated current (power)	13 A
Rated voltage (power)	600 V AC
Limiting temperature	-25 ... +80 °C
Cable diameter	9 mm

### Material properties

Material (cable)	PUR (polyurethane)
------------------	--------------------

## Material properties

Colour (cable)	Black
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	567c8b78-5fa0-43aa-a4c0-beb9d99b7769
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

## Specifications and approvals

Approvals	CE
-----------	----

## Commercial data

Packaging size	1
Net weight	190 g
Country of origin	Germany
European customs tariff number	85444290
GTIN	5713140816497
eCl@ss	27060311 Assembled sensor actuator-line
ETIM	EC001855
UNSPSC 24.0	26121604