

M8 Assy shielded 4-poles st/st m/m 2,0m



Image is for illustration purposes only. Please refer to product description.

Part number	21 34 737 3466 020
Specification	M8 Assy shielded 4-poles st/st m/m 2,0m
HARTING eCatalogue	https://harting.com/21347373466020

Identification

Category	System cabling
Series	Circular connectors M8
Element	Cable assemblies
Specification	Pre-assembled on both sides
Connector 1	M8 A-coding Male Straight
Connector 2	M8 A-coding Male Straight
Type of cable	Copper cable (round)

Version

Cable length	2 m
Number of cores	4
Core structure	4x 0.25 mm ²
Shielding	Shielded
Coding	A-coding

Technical characteristics

Limiting temperature	-25 ... +80 °C
----------------------	----------------

Material properties

Material (cable)	PVC
Colour (cable)	Grey
RoHS	compliant with exemption



Pushing Performance
 Since 1945

Material properties

RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	0d7d3693-d625-47ab-934a-d241bf72c86e
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead

Commercial data

Packaging size	1
Net weight	1 g
Country of origin	Czechia
European customs tariff number	85444290
GTIN	5713140249011
eCl@ss	27060390 Ready-made data cable (unspecified)
ETIM	EC002599
UNSPSC 24.0	26121600