

## M12 A 4pol m/f st/st PUR shld 15mt.



Image is for illustration purposes only. Please refer to product description.

|                    |                                                                                     |
|--------------------|-------------------------------------------------------------------------------------|
| Part number        | 21 34 787 5474 150                                                                  |
| Specification      | M12 A 4pol m/f st/st PUR shld 15mt.                                                 |
| HARTING eCatalogue | <a href="https://harting.com/21347875474150">https://harting.com/21347875474150</a> |

### Identification

|               |                                 |
|---------------|---------------------------------|
| Category      | System cabling                  |
| Series        | Circular connectors M12         |
| Element       | Cable assemblies                |
| Specification | Pre-assembled on both sides     |
| Connector 1   | M12 A-coding<br>Male Straight   |
| Connector 2   | M12 A-coding<br>Female Straight |
| Type of cable | Copper cable (round)            |

### Version

|                 |                         |
|-----------------|-------------------------|
| Cable length    | 15 m                    |
| Number of cores | 4                       |
| Core structure  | 4x 0.34 mm <sup>2</sup> |
| Shielding       | Shielded                |
| Coding          | A-coding                |

### Technical characteristics

|                      |                |
|----------------------|----------------|
| Limiting temperature | -25 ... +80 °C |
|----------------------|----------------|

### Material properties

|                  |                          |
|------------------|--------------------------|
| Material (cable) | PUR (polyurethane)       |
| Colour (cable)   | Black                    |
| RoHS             | compliant with exemption |



**Pushing Performance**  
 Since 1945

## Material properties

|                                      |                                                        |
|--------------------------------------|--------------------------------------------------------|
| RoHS exemptions                      | 6(c): Copper alloy containing up to 4 % lead by weight |
| ELV status                           | compliant with exemption                               |
| China RoHS                           | 50                                                     |
| REACH Annex XVII substances          | Not contained                                          |
| REACH ANNEX XIV substances           | Not contained                                          |
| REACH SVHC substances                | Yes                                                    |
| REACH SVHC substances                | Lead                                                   |
| ECHA SCIP number                     | 0d7d3693-d625-47ab-934a-d241bf72c86e                   |
| California Proposition 65 substances | Yes                                                    |
| California Proposition 65 substances | Lead<br>Nickel                                         |

## Commercial data

|                                |                                         |
|--------------------------------|-----------------------------------------|
| Packaging size                 | 10                                      |
| Net weight                     | 653.3 g                                 |
| Country of origin              | Czechia                                 |
| European customs tariff number | 85444290                                |
| GTIN                           | 5713140264502                           |
| eCl@ss                         | 27060311 Assembled sensor actuator-line |
| ETIM                           | EC002599                                |
| UNSPSC 24.0                    | 26121604                                |