

M12 A-cod 5-pol st/st m/f PUR 1.0m



Image is for illustration purposes only. Please refer to product description.

Part number	21 34 787 5568 010
Specification	M12 A-cod 5-pol st/st m/f PUR 1.0m
HARTING eCatalogue	https://harting.com/21347875568010

Identification

Category	System cabling
Series	Circular connectors M12
Element	Cable assemblies
Specification	Pre-assembled on both sides
Connector 1	M12 A-coding Male Straight
Connector 2	M12 A-coding Female Straight
Type of cable	Copper cable (round)

Version

Cable length	1 m
Number of cores	5
Core structure	5x 0.25 mm ²
Shielding	Shielded
Coding	A-coding

Technical characteristics

Limiting temperature	-25 ... +80 °C
----------------------	----------------

Material properties

Material (cable)	PUR (polyurethane)
Colour (cable)	Black
RoHS	compliant



Pushing Performance
Since 1945

Material properties

ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained

Commercial data

Packaging size	1
Net weight	72.14 g
Country of origin	Czechia
European customs tariff number	85444290
GTIN	5713140264656
eCl@ss	27060311 Assembled sensor actuator-line
ETIM	EC002599
UNSPSC 24.0	26121604