

M12 DeviceNet P+S A-cod st/st m/f 25,0m



Image is for illustration purposes only. Please refer to product description.

Part number	21 34 787 5572 250
Specification	M12 DeviceNet P+S A-cod st/st m/f 25,0m
HARTING eCatalogue	https://harting.com/21347875572250

Identification

Category	System cabling
Series	Circular connectors M12
Element	Cable assemblies
Specification	Pre-assembled on both sides
Connector 1	M12 A-coding Male Straight
Connector 2	M12 A-coding Female Straight
Type of cable	Copper cable (round)

Version

Cable length	25 m
Number of cores	4
Core structure	2x AWG 22 2x AWG 24
Coding	A-coding

Technical characteristics

Limiting temperature	-25 ... +80 °C
----------------------	----------------

Material properties

Material (cable)	PUR (polyurethane)
Colour (cable)	Black



Pushing Performance
Since 1945

Commercial data

Packaging size	1
Country of origin	Germany
European customs tariff number	85444290
GTIN	5713140815339
eCl@ss	27060311 Assembled sensor actuator-line
ETIM	EC002599
UNSPSC 24.0	26121604