

## M12 A 4pol m/f st/an PUR shld 0,3mt



Image is for illustration purposes only. Please refer to product description.

|                    |                                                                                     |
|--------------------|-------------------------------------------------------------------------------------|
| Part number        | 21 34 787 7474 003                                                                  |
| Specification      | M12 A 4pol m/f st/an PUR shld 0,3mt                                                 |
| HARTING eCatalogue | <a href="https://harting.com/21347877474003">https://harting.com/21347877474003</a> |

### Identification

|               |                               |
|---------------|-------------------------------|
| Category      | System cabling                |
| Series        | Circular connectors M12       |
| Element       | Cable assemblies              |
| Specification | Pre-assembled on both sides   |
| Connector 1   | M12 A-coding<br>Male Straight |
| Connector 2   | M12 A-coding<br>Female Angled |
| Type of cable | Copper cable (round)          |

### Version

|                 |                         |
|-----------------|-------------------------|
| Cable length    | 0.3 m                   |
| Number of cores | 4                       |
| Core structure  | 4x 0.34 mm <sup>2</sup> |
| Shielding       | Shielded                |
| Coding          | A-coding                |

### Technical characteristics

|                      |                |
|----------------------|----------------|
| Limiting temperature | -30 ... +80 °C |
|----------------------|----------------|

### Material properties

|                  |                          |
|------------------|--------------------------|
| Material (cable) | PUR (polyurethane)       |
| Colour (cable)   | Black                    |
| RoHS             | compliant with exemption |



**Pushing Performance**  
Since 1945

## Material properties

|                                      |                                                        |
|--------------------------------------|--------------------------------------------------------|
| RoHS exemptions                      | 6(c): Copper alloy containing up to 4 % lead by weight |
| ELV status                           | compliant with exemption                               |
| China RoHS                           | 50                                                     |
| REACH Annex XVII substances          | Not contained                                          |
| REACH ANNEX XIV substances           | Not contained                                          |
| REACH SVHC substances                | Yes                                                    |
| REACH SVHC substances                | Lead                                                   |
| ECHA SCIP number                     | 567c8b78-5fa0-43aa-a4c0-beb9d99b7769                   |
| California Proposition 65 substances | Yes                                                    |
| California Proposition 65 substances | Lead                                                   |
|                                      | Nickel                                                 |

## Commercial data

|                                |                                         |
|--------------------------------|-----------------------------------------|
| Packaging size                 | 10                                      |
| Net weight                     | 41 g                                    |
| Country of origin              | Germany                                 |
| European customs tariff number | 85444290                                |
| GTIN                           | 5713140265028                           |
| eCl@ss                         | 27060311 Assembled sensor actuator-line |
| ETIM                           | EC002599                                |
| UNSPSC 24.0                    | 26121604                                |