

M12 Cable Assembly A-cod st/st f/m 0,5m



Image is for illustration purposes only. Please refer to product description.

Part number	21 34 848 5C78 005
Specification	M12 Cable Assembly A-cod st/st f/m 0,5m
HARTING eCatalogue	https://harting.com/21348485C78005

Identification

Category	System cabling
Series	Circular connectors M12
Element	Cable assemblies
Specification	Pre-assembled on both sides
Connector 1	M12 A-coding Male Straight
Connector 2	M12 A-coding Female Straight
Type of cable	Copper cable (round)

Version

Cable length	0.5 m
Number of cores	12
Core structure	12x 0.14 mm ²
Coding	A-coding

Material properties

Material (cable)	PUR (polyurethane)
Colour (cable)	Black
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained



Pushing Performance
 Since 1945

Material properties

REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	0d7d3693-d625-47ab-934a-d241bf72c86e
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead

Specifications and approvals

Approvals	CE
-----------	----

Commercial data

Packaging size	1
Net weight	44.4 g
Country of origin	Germany
European customs tariff number	85444290
GTIN	5713140142619
eCl@ss	27060311 Assembled sensor actuator-line
ETIM	EC002599
UNSPSC 24.0	26121604