

## M12 Cable Assembly A-cod st/st f/m 1,5m



Image is for illustration purposes only. Please refer to product description.

Part number	21 34 848 5C79 015
Specification	M12 Cable Assembly A-cod st/st f/m 1,5m
HARTING eCatalogue	<a href="https://harting.com/21348485C79015">https://harting.com/21348485C79015</a>

### Identification

Category	System cabling
Series	Circular connectors M12
Element	Cable assemblies
Specification	Pre-assembled on both sides
Connector 1	M12 A-coding Male Straight
Connector 2	M12 A-coding Female Straight
Type of cable	Copper cable (round)

### Version

Cable length	1.5 m
Number of cores	12
Core structure	12x 0.14 mm <sup>2</sup>
Coding	A-coding

### Material properties

Material (cable)	PVC
Colour (cable)	Grey
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained



**Pushing Performance**  
Since 1945

## Material properties

REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	0d7d3693-d625-47ab-934a-d241bf72c86e
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead

## Specifications and approvals

Approvals	CE
-----------	----

## Commercial data

Packaging size	1
Net weight	102.5 g
Country of origin	Germany
European customs tariff number	85444290
GTIN	5713140142701
eCl@ss	27060311 Assembled sensor actuator-line
ETIM	EC002599
UNSPSC 24.0	26121604