

M12 A-coded Cable Assembly



Image is for illustration purposes only. Please refer to product description.

Part number	21 34 870 0C78 015
Specification	M12 A-coded Cable Assembly
HARTING eCatalogue	https://harting.com/21348700C78015

Identification

Category	System cabling
Series	Circular connectors M12
Element	Cable assemblies
Specification	Pre-assembled on one side
Connector 1	M12 A-coding Female Angled
Type of cable	Copper cable (round)

Version

Cable length	1.5 m
Number of cores	12
Core structure	12x 0.14 mm ²
Coding	A-coding

Material properties

Material (cable)	PUR (polyurethane)
Colour (cable)	Black
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained



Pushing Performance
Since 1945

Material properties

REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	0d7d3693-d625-47ab-934a-d241bf72c86e
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead

Specifications and approvals

Approvals	CE
-----------	----

Commercial data

Packaging size	1
Net weight	82 g
Country of origin	Germany
European customs tariff number	85444290
GTIN	5713140144149
eCl@ss	27060311 Assembled sensor actuator-line
ETIM	EC001855
UNSPSC 24.0	26121604