

## M12 A-coded Cable Assembly



Image is for illustration purposes only. Please refer to product description.

Part number	21 34 870 0C78 050
Specification	M12 A-coded Cable Assembly
HARTING eCatalogue	<a href="https://harting.com/21348700C78050">https://harting.com/21348700C78050</a>

### Identification

Category	System cabling
Series	Circular connectors M12
Element	Cable assemblies
Specification	Pre-assembled on one side
Connector 1	M12 A-coding Female Angled
Type of cable	Copper cable (round)

### Version

Cable length	5 m
Number of cores	12
Core structure	12x 0.14 mm <sup>2</sup>
Coding	A-coding

### Material properties

Material (cable)	PUR (polyurethane)
Colour (cable)	Black
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes



**Pushing Performance**  
Since 1945

## Material properties

REACH SVHC substances	Lead
ECHA SCIP number	0d7d3693-d625-47ab-934a-d241bf72c86e

## Specifications and approvals

Approvals	CE
-----------	----

## Commercial data

Packaging size	1
Net weight	240 g
Country of origin	Slovakia
European customs tariff number	85444290
GTIN	5713140144163
eCl@ss	27060311 Assembled sensor actuator-line
ETIM	EC001855
UNSPSC 24.0	26121604