

M12 Cable Assembly D-cod st/- f/- 0,5m



Image is for illustration purposes only. Please refer to product description.

Part number	21 34 930 0477 005
Specification	M12 Cable Assembly D-cod st/- f/- 0,5m
HARTING eCatalogue	https://harting.com/21349300477005

Identification

Category	System cabling
Series	Circular connectors M12
Element	Cable assemblies
Specification	Pre-assembled on one side
Connector 1	M12 D-coding Female Straight
Type of cable	Copper cable (round)

Version

Cable length	0.5 m
Number of cores	4
Core structure	4x AWG 22/7
Coding	D-coding

Technical characteristics

Transmission characteristics	Cat. 5 Class D up to 100 MHz
Data rate	10 Mbit/s 100 Mbit/s

Material properties

Material (cable)	PUR (polyurethane)
Colour (cable)	Green
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight



Pushing Performance
Since 1945

Material properties

ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	0d7d3693-d625-47ab-934a-d241bf72c86e
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead

Specifications and approvals

Specifications	UN/ECE-R 118 fire protection for rolling stock
Approvals	CE

Commercial data

Packaging size	1
Net weight	47.5 g
Country of origin	Germany
European customs tariff number	85444290
GTIN	5713140145498
eCl@ss	27060390 Ready-made data cable (unspecified)
ETIM	EC002599
UNSPSC 24.0	26121600