

M12 Cable Assembly D-cod an/- f/- 1,0m



Image is for illustration purposes only. Please refer to product description.

Part number	21 34 950 0477 010
Specification	M12 Cable Assembly D-cod an/- f/- 1,0m
HARTING eCatalogue	https://harting.com/21349500477010

Identification

Category	System cabling
Series	Circular connectors M12
Element	Cable assemblies
Specification	Pre-assembled on one side
Connector 1	M12 D-coding Female Angled
Type of cable	Copper cable (round)

Version

Cable length	1 m
Number of cores	4
Core structure	4x AWG 22/7
Coding	D-coding

Technical characteristics

Transmission characteristics	Cat. 5 Class D up to 100 MHz
Data rate	10 Mbit/s 100 Mbit/s

Material properties

Material (cable)	PUR (polyurethane)
Colour (cable)	Green
RoHS	compliant
ELV status	compliant



Pushing Performance
Since 1945

Material properties

China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained

Specifications and approvals

Specifications	UN/ECE-R 118 fire protection for rolling stock
Approvals	CE

Commercial data

Packaging size	1
Net weight	82.6 g
Country of origin	Germany
European customs tariff number	85444290
GTIN	5713140145931
eCl@ss	27060390 Ready-made data cable (unspecified)
ETIM	EC002599
UNSPSC 24.0	26121600