

## M12 A-cod 4-pol st/st m/f PVC 10m



Image is for illustration purposes only. Please refer to product description.

Part number	21 35 010 2416 100
Specification	M12 A-cod 4-pol st/st m/f PVC 10m
HARTING eCatalogue	<a href="https://harting.com/21350102416100">https://harting.com/21350102416100</a>

### Identification

Category	System cabling
Series	Circular connectors M12
Element	Cable assemblies
Specification	Pre-assembled on both sides
Connector 1	M12 A-coding Male Straight
Connector 2	M12 A-coding Female Straight
Type of cable	Copper cable (round)

### Version

Cable length	10 m
Number of cores	4
Core structure	4x 0.34 mm <sup>2</sup>
Coding	A-coding

### Material properties

Material (cable)	PVC
Colour (cable)	Yellow

### Commercial data

Packaging size	1
Net weight	371.089 g
Country of origin	Mexico

## Commercial data

GTIN	5713140811744
eCl@ss	27060311 Assembled sensor actuator-line
UNSPSC 24.0	26121604