

## M23\_19P FE,Int-thread,ANG PVC cable,5M



Image is for illustration purposes only. Please refer to product description.

|                    |                                                                                     |
|--------------------|-------------------------------------------------------------------------------------|
| Part number        | 21 37 360 0D75 050                                                                  |
| Specification      | M23_19P FE,Int-thread,ANG PVC cable,5M                                              |
| HARTING eCatalogue | <a href="https://harting.com/21373600D75050">https://harting.com/21373600D75050</a> |

### Identification

|                |                                                                  |
|----------------|------------------------------------------------------------------|
| Category       | System cabling                                                   |
| Series         | Circular connectors M23                                          |
| Identification | Signal                                                           |
| Element        | Cable assemblies                                                 |
| Specification  | Pre-assembled on one side                                        |
| Connector 1    | M23<br>Female Angled                                             |
| Type of cable  | Copper cable (round)                                             |
| Features       | Flame retardancy<br>Oil and UV resistant<br>Highly EMC resistant |

### Version

|                 |                        |
|-----------------|------------------------|
| Cable length    | 5 m                    |
| Number of cores | 19                     |
| Core structure  | 3x AWG 18 + 16x AWG 22 |

### Technical characteristics

|                                        |                |
|----------------------------------------|----------------|
| Rated voltage                          | 150 V          |
| Rated current (signal)                 | 2 A            |
| Rated current (power)                  | 9 A            |
| Limiting temperature                   | -40 ... +80 °C |
| Degree of protection acc. to IEC 60529 | IP67           |



**Pushing Performance**  
 Since 1945

## Material properties

|                                      |                                                        |
|--------------------------------------|--------------------------------------------------------|
| Material (contacts)                  | Copper alloy                                           |
| Surface (contacts)                   | Silver plated                                          |
| Material (cable)                     | PVC                                                    |
| Colour (cable)                       | Black                                                  |
| Material (overmoulding)              | Thermoplastic polyurethane (TPU)                       |
| Colour (overmoulding)                | Black                                                  |
| RoHS                                 | compliant with exemption                               |
| RoHS exemptions                      | 6(c): Copper alloy containing up to 4 % lead by weight |
| ELV status                           | compliant with exemption                               |
| China RoHS                           | 50                                                     |
| REACH Annex XVII substances          | Not contained                                          |
| REACH ANNEX XIV substances           | Not contained                                          |
| REACH SVHC substances                | Yes                                                    |
| REACH SVHC substances                | Lead                                                   |
| ECHA SCIP number                     | 567c8b78-5fa0-43aa-a4c0-beb9d99b7769                   |
| California Proposition 65 substances | Yes                                                    |
| California Proposition 65 substances | Lead<br>Nickel                                         |

## Commercial data

|                                |                                         |
|--------------------------------|-----------------------------------------|
| Packaging size                 | 1                                       |
| Country of origin              | China                                   |
| European customs tariff number | 85444290                                |
| GTIN                           | 5713140241329                           |
| eCl@ss                         | 27060311 Assembled sensor actuator-line |
| ETIM                           | EC001855                                |
| UNSPSC 24.0                    | 26121604                                |