

## M17 MA str molded 6+PE PUR open end,10m



Image is for illustration purposes only. Please refer to product description.

Part number	21 37 510 0701 100
Specification	M17 MA str molded 6+PE PUR open end,10m
HARTING eCatalogue	<a href="https://harting.com/21375100701100">https://harting.com/21375100701100</a>

### Identification

Category	System cabling
Series	Circular connectors M17
Element	Cable assemblies
Specification	Pre-assembled on one side
Connector 1	M17 Overmoulded Male Straight
Type of cable	Copper cable (round)

### Version

Cable length	10 m
Number of cores	7
Core structure	6x 0.5 mm <sup>2</sup> + 1 mm <sup>2</sup>

### Technical characteristics

Rated current	8 A
Rated voltage	300 V
Limiting temperature	-20 ... +80 °C
Degree of protection acc. to IEC 60529	IP65 IP67

### Material properties

Material (cable)	PUR (polyurethane)
Colour (cable)	Black
RoHS	compliant with exemption

## Material properties

RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	567c8b78-5fa0-43aa-a4c0-beb9d99b7769
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

## Commercial data

Packaging size	1
Country of origin	China
European customs tariff number	85444290
GTIN	5713140240711
eCl@ss	27060311 Assembled sensor actuator-line
ETIM	EC001855
UNSPSC 24.0	26121604