

M17 FE str molded 6+PE PUR open end,5m



Image is for illustration purposes only. Please refer to product description.

Part number	21 37 520 0701 050
Specification	M17 FE str molded 6+PE PUR open end,5m
HARTING eCatalogue	https://harting.com/21375200701050

Identification

Category	System cabling
Series	Circular connectors M17
Element	Cable assemblies
Specification	Pre-assembled on one side
Connector 1	M17 Overmoulded Female Straight
Type of cable	Copper cable (round)

Version

Cable length	5 m
Number of cores	7
Core structure	6x 0.5 mm ² + 1 mm ²

Technical characteristics

Rated current	8 A
Rated voltage	300 V
Limiting temperature	-20 ... +80 °C
Degree of protection acc. to IEC 60529	IP65 IP67

Material properties

Material (cable)	PUR (polyurethane)
Colour (cable)	Black
RoHS	compliant with exemption



Pushing Performance
 Since 1945

Material properties

RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	567c8b78-5fa0-43aa-a4c0-beb9d99b7769
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

Commercial data

Packaging size	1
Net weight	542 g
Country of origin	China
European customs tariff number	85444290
GTIN	5713140240728
eCl@ss	27060311 Assembled sensor actuator-line
ETIM	EC001855
UNSPSC 24.0	26121604