

M12 A-cod 8-pol st/- m/- PVC PP 0.5m



Image is for illustration purposes only. Please refer to product description.

Part number	21 40 200 0883 005
Specification	M12 A-cod 8-pol st/- m/- PVC PP 0.5m
HARTING eCatalogue	https://harting.com/21402000883005

Identification

Category	System cabling
Series	Circular connectors M12
Element	Cable assemblies
Specification	Pre-assembled on one side
Connector 1	M12 A-coding Male Straight
Type of cable	Copper cable (round)

Version

Cable length	0.5 m
Number of cores	8
Core structure	8x AWG 24/7
Shielding	Shielded
Number of contacts	8
Coding	A-coding
Locking type	PushPull

Technical characteristics

Rated voltage	30 V AC 30 V DC
Limiting temperature	-40 ... +80 °C
Degree of protection acc. to IEC 60529	IP65 / IP67 mated condition
Cable diameter	6.5 mm ± 0.2 mm



Pushing Performance
Since 1945

Material properties

Material (cable)	PVC
Colour (cable)	Grey
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	567c8b78-5fa0-43aa-a4c0-beb9d99b7769
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

Commercial data

Packaging size	1
Net weight	101 g
Country of origin	Romania
European customs tariff number	85444290
GTIN	5713140342194
eCl@ss	27060311 Assembled sensor actuator-line
UNSPSC 24.0	26121604