

M12 A-cod 3-pol an/- m/- PUR PP 5.0m



Image is for illustration purposes only. Please refer to product description.

Part number	21 40 220 0332 050
Specification	M12 A-cod 3-pol an/- m/- PUR PP 5.0m
HARTING eCatalogue	https://harting.com/21402200332050

Identification

Category	System cabling
Series	Circular connectors M12
Element	Cable assemblies
Specification	Pre-assembled on one side
Connector 1	M12 A-coding Male Angled
Type of cable	Copper cable (round)

Version

Cable length	5 m
Number of cores	3
Core structure	3x 0.34 mm ²
Shielding	Shielded
Number of contacts	3
Coding	A-coding
Locking type	PushPull

Technical characteristics

Rated voltage	48 V AC 60 V DC
Limiting temperature	-50 ... +80 °C moved -30 ... +80 °C unmoved
Degree of protection acc. to IEC 60529	IP65 / IP67 mated condition
Cable diameter	4.1 mm ± 0.2 mm

Technical characteristics

Minimum bending radius	5x Cable diameter (singular bending) 10x Cable diameter (repeated bending)
------------------------	---

Material properties

Material (cable)	PUR (polyurethane)
Colour (cable)	Black
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Commercial data

Packaging size	1
Net weight	178 g
Country of origin	Romania
European customs tariff number	85444290
GTIN	5713140491489
eCl@ss	27060311 Assembled sensor actuator-line
UNSPSC 24.0	26121604