

M12 A-cod 4-pol an/- m/- PUR PP 1.5m




Image is for illustration purposes only. Please refer to product description.

Part number	21 40 220 0442 015
Specification	M12 A-cod 4-pol an/- m/- PUR PP 1.5m
HARTING eCatalogue	https://harting.com/21402200442015

Identification

Category	System cabling
Series	Circular connectors M12
Element	Cable assemblies
Specification	Pre-assembled on one side
Connector 1	M12 A-coding Male Angled
Type of cable	Copper cable (round)

Version

Cable length	1.5 m
Number of cores	4
Core structure	4x 0.34 mm ²
Shielding	Shielded
Number of contacts	4
Coding	A-coding
Locking type	PushPull

Technical characteristics

Rated voltage	48 V AC 60 V DC
Limiting temperature	-50 ... +80 °C moved -30 ... +80 °C unmoved
Degree of protection acc. to IEC 60529	IP65 / IP67 mated condition
Cable diameter	4.4 mm ± 0.2 mm



Pushing Performance
Since 1945

Technical characteristics

Minimum bending radius	5x Cable diameter (singular bending)
	10x Cable diameter (repeated bending)

Material properties

Material (cable)	PUR (polyurethane)
Colour (cable)	Black
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	760691ac-b4d2-427c-9996-5886190b813b
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead

Commercial data

Packaging size	1
Net weight	75 g
Country of origin	Romania
European customs tariff number	85444290
GTIN	5713140341586
eCl@ss	27060311 Assembled sensor actuator-line
UNSPSC 24.0	26121604