

M12 X-cod 8-pol an/an m/m PUR PP 1.5m



Image is for illustration purposes only. Please refer to product description.

Part number	21 40 626 2886 015
Specification	M12 X-cod 8-pol an/an m/m PUR PP 1.5m
HARTING eCatalogue	https://harting.com/21406262886015

Identification

Category	System cabling
Series	Circular connectors M12
Element	Cable assemblies
Specification	Pre-assembled on both sides
Connector 1	M12 X-coding Male Angled
Connector 2	M12 X-coding Male Angled
Type of cable	Copper cable (round)

Version

Cable length	1.5 m
Number of cores	8
Core structure	4x 2x AWG 26/7
Shielding	Shielded
Number of contacts	8
Coding	X-coding
Locking type	PushPull

Technical characteristics

Rated current	0.5 A
Rated voltage	48 V AC 60 V DC
Transmission characteristics	Cat. 6 _A Class E _A up to 500 MHz



Pushing Performance
Since 1945

Technical characteristics

Limiting temperature	-40 ... +80 °C moved -40 ... +80 °C unmoved
Degree of protection acc. to IEC 60529	IP65 / IP67 mated condition
Cable diameter	6.7 mm ± 0.3 mm
Minimum bending radius	5x Cable diameter (singular bending) 10x Cable diameter (repeated bending)

Material properties

Material (cable)	PUR (polyurethane)
Colour (cable)	Yellow

Specifications and approvals

Specifications	UN/ECE-R 118
----------------	--------------

Commercial data

Packaging size	1
Net weight	95 g
Country of origin	Romania
European customs tariff number	85444290
GTIN	5713140342613
eCl@ss	27060390 Ready-made data cable (unspecified)
UNSPSC 24.0	26121600