

PFT-housing with bayonet locking notch



Image is for illustration purposes only. Please refer to product description.

Part number	21 96 339 9000
Specification	PFT-housing with bayonet locking notch
HARTING eCatalogue	https://harting.com/21963399000

Identification

Category	Hoods / Housings
Series	Circular connectors B17
Type of hood/housing	Bulkhead mounted housing
Description of hood/housing	Straight Front mounting

Version

Size	B17
Fixing	Fixing hole 4x 2.8 mm
Locking type	Bayonet locking

Technical characteristics

Limiting temperature	-30 ... +85 °C
Degree of protection acc. to IEC 60529	IP65 / IP67 locked condition

Material properties

Material (hood/housing)	Zinc alloy
Surface (hood/housing)	Nickel plated
Material (seal)	NBR
Colour (seal)	Black
RoHS	compliant
ELV status	compliant
China RoHS	e



Pushing Performance
Since 1945

Material properties

REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Specifications and approvals

Specifications	Inspired by IEC 61076-2-118
UL / CSA	UL 2237 / 2238 in preparation

Commercial data

Packaging size	1
Net weight	26.92 g
Country of origin	Taiwan
European customs tariff number	85389099
eCl@ss	27440224 Shell for circular connectors
UNSPSC 24.0	39121405