

har-flex, 40p, with sr, PVC, L=300mm



Image is for illustration purposes only. Please refer to product description.

Part number	33 15 243 0300 103
Specification	har-flex, 40p, with sr, PVC, L=300mm
HARTING eCatalogue	https://harting.com/33152430300103

Identification

Category	System cabling
Series	har-flex®
Element	Cable assemblies
Specification	Pre-assembled on both sides
Connector 1	har-flex®
	Female connector
	With strain relief
Connector 2	har-flex®
	Female connector
	With strain relief
	Different connector direction
Type of cable	Copper cable (flat)

Version

Cable length	0.3 m
Number of cores	40
Core structure	40x AWG 30

Technical characteristics

Contact spacing (mating side)	1.27 mm
-------------------------------	---------

Material properties

Material (cable)	PVC
Colour (cable)	Grey
RoHS	compliant



Pushing Performance
Since 1945

Material properties

ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Antimony trioxide Lead

Commercial data

Packaging size	1
Net weight	18.28 g
Country of origin	China
European customs tariff number	85444290
GTIN	5713140245372
eCl@ss	27060390 Ready-made data cable (unspecified)
ETIM	EC002599
UNSPSC 24.0	26121600