

HARLINK MA DE IEEE1355 CABLE ASSY,L=0.5M



Image is for illustration purposes only. Please refer to product description.

Part number	33 27 243 0500 015
Specification	HARLINK MA DE IEEE1355 CABLE ASSY,L=0.5M
HARTING eCatalogue	https://harting.com/33272430500015

Identification

Category	System cabling
Series	har-link®
Element	Cable assemblies
Specification	Pre-assembled on both sides
Connector 1	har-link®
Connector 2	har-link®
Type of cable	Copper cable (round)
Description of the cable	Wiring acc. to IEEE 1355

Version

Cable length	0.5 m
Number of cores	10
Core structure	10x AWG 30

Material properties

Material (cable)	PVC
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes



Pushing Performance
Since 1945

Material properties

California Proposition 65 substances	Nickel
--------------------------------------	--------

Commercial data

Packaging size	1
Net weight	37.3 g
Country of origin	China
European customs tariff number	85444290
GTIN	5713140245846
eCl@ss	27060390 Ready-made data cable (unspecified)
ETIM	EC002599
UNSPSC 24.0	26121600