

## Han 1A OM 5+PE -lever m/ - PVC 5m



Image is for illustration purposes only. Please refer to product description.

|                    |                                                                                     |
|--------------------|-------------------------------------------------------------------------------------|
| Part number        | 33 40 060 0201 050                                                                  |
| Specification      | Han 1A OM 5+PE -lever m/ - PVC 5m                                                   |
| HARTING eCatalogue | <a href="https://harting.com/33400600201050">https://harting.com/33400600201050</a> |

### Identification

|                          |                             |
|--------------------------|-----------------------------|
| Category                 | System cabling              |
| Series                   | Han® 1A                     |
| Element                  | Cable assemblies            |
| Specification            | Pre-assembled on one side   |
| Connector 1              | Han® 1A Male<br>Overmoulded |
| Type of cable            | Copper cable (round)        |
| Description of the cable | Oil resistant               |

### Version

|                    |                                                                                                                                                                                 |
|--------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Cable length       | 5 m                                                                                                                                                                             |
| Number of cores    | 6                                                                                                                                                                               |
| Core structure     | 6x 1.5 mm <sup>2</sup>                                                                                                                                                          |
| Number of contacts | 5                                                                                                                                                                               |
| PE contact         | Yes                                                                                                                                                                             |
| Locking type       | Single locking lever                                                                                                                                                            |
| Details            | Not be coupled or decoupled under electrical load.<br>Assembly and installation must be carried out by a qualified electrician.<br>IP66 / IP67 in mated cable to cable position |

### Technical characteristics

|                               |       |
|-------------------------------|-------|
| Rated current                 | 10 A  |
| Rated voltage                 | 400 V |
| Rated voltage conductor-earth | 300 V |



**Pushing Performance**  
 Since 1945

## Technical characteristics

|                                        |                                                                      |
|----------------------------------------|----------------------------------------------------------------------|
| Limiting temperature                   | -30 ... +80 °C unmoved<br>-15 ... +80 °C moved                       |
| Mating cycles                          | ≥100                                                                 |
| Degree of protection acc. to IEC 60529 | IP65 mated condition<br>IP66 mated condition<br>IP67 mated condition |
| Cable diameter                         | 9.2 mm                                                               |

## Material properties

|                                      |                                                        |
|--------------------------------------|--------------------------------------------------------|
| Material (cable)                     | PVC                                                    |
| Colour (cable)                       | Grey                                                   |
| RoHS                                 | compliant with exemption                               |
| RoHS exemptions                      | 6(c): Copper alloy containing up to 4 % lead by weight |
| ELV status                           | compliant with exemption                               |
| China RoHS                           | 50                                                     |
| REACH Annex XVII substances          | Not contained                                          |
| REACH ANNEX XIV substances           | Not contained                                          |
| REACH SVHC substances                | Yes                                                    |
| REACH SVHC substances                | Lead                                                   |
| ECHA SCIP number                     | 567c8b78-5fa0-43aa-a4c0-beb9d99b7769                   |
| California Proposition 65 substances | Yes                                                    |
| California Proposition 65 substances | Lead                                                   |

## Specifications and approvals

|                |                                |
|----------------|--------------------------------|
| Specifications | IEC 60332-1-2 Flame retardancy |
|----------------|--------------------------------|

## Commercial data

|                                |                                         |
|--------------------------------|-----------------------------------------|
| Packaging size                 | 2                                       |
| Country of origin              | Romania                                 |
| European customs tariff number | 85444290                                |
| GTIN                           | 5713140237315                           |
| eCl@ss                         | 27060311 Assembled sensor actuator-line |
| ETIM                           | EC001855                                |
| UNSPSC 24.0                    | 26121604                                |