

## ix Ind. - DB RJ45 Cat.6A FRNC red 3,0m



Image is for illustration purposes only. Please refer to product description.

Part number	33 48 014 7825 030
Specification	ix Ind. - DB RJ45 Cat.6A FRNC red 3,0m
HARTING eCatalogue	<a href="https://harting.com/33480147825030">https://harting.com/33480147825030</a>

### Identification

Category	System cabling
Series	HARTING ix Industrial® RJ45
Element	Cable assemblies
Specification	Pre-assembled on both sides
Connector 1	HARTING ix Industrial® Type A
Connector 2	RJ45
Type of cable	Copper cable (round)

### Version

Cable length	3 m
Number of cores	8
Core structure	4x 2x AWG 26/7
Termination method	IDC insulation displacement termination

### Technical characteristics

Transmission characteristics	Cat. 6A Class EA up to 500 MHz
	10 Mbit/s
	100 Mbit/s
Data rate	1 Gbit/s
	2.5 Gbit/s
	5 Gbit/s
	10 Gbit/s
Limiting temperature	-20 ... +60 °C

## Material properties

Material (cable)	FRNC (LSZH)
Colour (cable)	Red
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

## Specifications and approvals

Specifications	IEC 61076-3-124 IEC 60332-1 Flame retardancy IEC 60754-2 Halogen freeness IEC 61034 Smoke density
----------------	--

## Commercial data

Packaging size	1
Net weight	130 g
Country of origin	Latvia
European customs tariff number	85444290
GTIN	5713140263727
eCl@ss	27060390 Ready-made data cable (unspecified)
ETIM	EC002599
UNSPSC 24.0	26121600