

## ix Ind Type A - RJ45 AWG28 Cat6A PVC 5m



Image is for illustration purposes only. Please refer to product description.

Part number	33 48 065 3830 050
Specification	ix Ind Type A - RJ45 AWG28 Cat6A PVC 5m
HARTING eCatalogue	<a href="https://harting.com/33480653830050">https://harting.com/33480653830050</a>

### Identification

Category	System cabling
Series	HARTING ix Industrial® RJ45
Element	Cable assemblies
Specification	Pre-assembled on both sides
Connector 1	HARTING ix Industrial® Type A Solder termination
Connector 2	RJ45 Piercing termination
Type of cable	Copper cable (round)

### Version

Cable length	5 m
Number of cores	8
Core structure	4x 2x AWG 28/7

### Technical characteristics

Transmission characteristics	Cat. 6A Class E <sub>A</sub> up to 500 MHz
	10 Mbit/s
	100 Mbit/s
	1 Gbit/s
	2.5 Gbit/s
	5 Gbit/s
	10 Gbit/s

## Technical characteristics

Limiting temperature	-40 ... +70 °C
----------------------	----------------

## Material properties

Material (cable)	PVC
Colour (cable)	Yellow
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel

## Specifications and approvals

Specifications	IEC 61076-3-124
----------------	-----------------

## Commercial data

Packaging size	1
Net weight	244 g
Country of origin	Vietnam
European customs tariff number	85444290
GTIN	5713140264175
eCl@ss	27060390 Ready-made data cable (unspecified)
ETIM	EC002599
UNSPSC 24.0	26121600